

EZ-IN™ MINI-SPLIT CABLE



APPLICATIONS

- **Voltage Rating:** 600 volts
- **Temperature Rating:** 90°C (*Dry*) and 75°C (*Wet*)
- **For use:** Indoors and outdoors in wet locations, direct burial
- Can be installed without the use of conduit

FEATURES

- **Moisture and Sunlight Resistant**

CONSTRUCTION

- **Conductor(s):** Stranded, bare copper THHN/THWN
- **Interlocked aluminum armor**
- **Jacket:** Flame retardant PVC jacket applied over the armor

SPECIFICATIONS

- The National Electrical Code® / NFPA 70
- ASTM B3, B787
- Conductors per UL Standard 83, Type THHN and THWN
- UL Standard 1569 for Type MC
- Rated for CT use
- Meets the material content restrictions of the RoHS-2 Directive

SIZE (AWG)	NO. OF COND.	NO. OF STRANDS	CONDUCTOR COLORS	INSULATION THICKNESS (MILS)	JACKET THICKNESS (MILS)	NOM. CABLE O.D. (MILS)	NOM. CABLE WEIGHT (LBS/1000FT)
16	4	7	Black, Red, White, Green	15/4	40	523	122
14	4	7	Black, Red, White, Green	15/4	40	553	148
14	7	7	Black, Red, Blue, Orange, Yellow, Brown, Red-Black	15/4	50	636	220