

# MINI-SPLIT TRAY CABLE

## 600 VOLT

### APPLICATIONS Suitable for use as follows:

- Tray Cable is a multi-conductor control, signal or power cable rated for 600 volts
- May be installed in raceways, conduit, cable trays and outdoor locations where supported by a messenger wire
- Also suitable for direct burial
- Temperature rated at 75°C wet locations / 90°C dry locations

### STANDARDS & REFERENCES

- UL listed as per UL 1277
- Conforms to applicable sections of UL 1581 and 1685
- RoHS Compliant
- Type TC

### CONSTRUCTION

- Stranded copper conductors Type THHN or THWN
- The overall jacket is heat, moisture and sunlight resistant PVC



**EZ-IN™ MINI-SPLIT CABLE 600 VOLT /  
MINI-SPLIT TRAY CABLE 600 VOLT**

### WEIGHTS, MEASUREMENTS, AND PACKAGING

| SIZE (AWG) / NUMBER OF CONDUCTORS | CONDUCTOR COLORS   | JACKET THICKNESS NOM. (mils) / COLOR | APPROX. O.D. (mils) | APPROX. NET WT. (lbs/1000 ft) |
|-----------------------------------|--|--------------------------------------|---------------------|-------------------------------|
| 14/4                              | Black, Red, Blue, Orange                                       | 45/Black                             | 350                 | 93                            |
| 14/7                              | Black, Red, Blue, Orange, Yellow, Brown, Red with Black Stripe | 45/Black                             | 413                 | 145                           |

600 Volt

90°C Dry

75°C Wet

PVC Jacket



greenSpec  
RoHS Compliant  
2002/95/EC



**Southwire®**